



A = EMITTER AXIS  
B = RECEIVER AXIS



ISOMETRIC VIEW

NOTES:

1. DIMENSIONS CAN BE CHANGED BY MANUFACTURER WITHOUT NOTICE.
2. DIMENSIONS DO NOT IMPLY TOLERANCE.

LLR-M12MA-NMK-101

Units: mm [inches]  
Scale: Full

CONTRINEX PHOTOELECTRIC SENSOR, TUBULAR  
THREADED, CHROME-PLATED BRASS HOUSING,  
THROUGH-BEAM RECEIVER, 0-10M SENSING  
DISTANCE, 10-30 VDC OPERATING VOLTAGE,  
COMPLEMENTARY LIGHT-ON/DARK-ON, NPN, 4-  
WIRE, PIGTAIL.