




A = EMITTER AXIS  
B = RECEIVER AXIS



ISOMETRIC VIEW

NOTES:

- 1. DIMENSIONS CAN BE CHANGED BY MANUFACTURER WITHOUT NOTICE.
- 2. DIMENSIONS DO NOT IMPLY TOLERANCE.

LLR-M12MA-NMK-603
Units: mm [inches] Scale: Full CONTRINEX PHOTOELECTRIC SENSOR, TUBULAR, THREADED, CHROME-PLATED BRASS HOUSING, THROUGH-BEAM RECEIVER, 0-10M SENSING DISTANCE, 10-30 VDC OPERATING VOLTAGE, COMPLEMENTARY LIGHT-ON/DARK-ON, PNP, 4- WIRE, PIGTAIL.
 <b>AUTOMATIONDIRECT</b> .com