




A = EMITTER AXIS
B = RECEIVER AXIS



ISOMETRIC VIEW

NOTES:

- 1. DIMENSIONS CAN BE CHANGED BY MANUFACTURER WITHOUT NOTICE.
- 2. DIMENSIONS DO NOT IMPLY TOLERANCE.

LLR-M12MA-NMS-400
Units: mm [inches] Scale: Full CONTRINEX PHOTOELECTRIC SENSOR, TUBULAR, THREADED, CHROME-PLATED BRASS HOUSING, THROUGH-BEAM EMITTER, VISIBLE RED LIGHT EMISSION, 0-10M SENSING DISTANCE, 10-30 VDC OPERATING VOLTAGE, 3-WIRE, 4-PIN M12 QUICK-DISCONNECT.
 AUTOMATIONDIRECT .com