






GENERAL NOTES:

1. ANALOG OUTPUT IS MAXIMUM WITH PROBE RETRACTED; SEE TECHNICAL DATA SHEET TO SPECIFY REVERSED OUTPUT.
2. SENSOR SUPPLIED WITH AGD #9 CONTACT TIP. (4-48 UNF THD)
3. SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE.



ISOMETRIC VIEW



LRSE18-050A-00-10A

Units: inches [mm]

Scale: Full

3/4" OD ALUMINUM BODY, 2"
RANGE, SPRING LOADED, AXIAL
1M CABLE

NOTES:

1. DIMENSIONS CAN BE CHANGED BY MANUFACTURER WITHOUT NOTICE.
2. DIMENSIONS DO NOT IMPLY TOLERANCE.