






GENERAL NOTES:

- 1. ANALOG OUTPUT IS MAXIMUM WITH PROBE RETRACTED; SEE TECHNICAL DATA SHEET TO SPECIFY REVERSED OUTPUT.
- 2. SENSOR SUPPLIED WITH AGD #9 CONTACT TIP. (4-48 UNF THD)
- 3. SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE.

2



ISOMETRIC VIEW



NOTES:

- 1. DIMENSIONS CAN BE CHANGED BY MANUFACTURER WITHOUT NOTICE.
- 2. DIMENSIONS DO NOT IMPLY TOLERANCE.

LRSI18-025A-00-20A

Units: inches [mm]
Scale: Full
3/4" OD, ALUMINUM BODY, 1"
RANGE, SPRING LOADED, AXIAL
1M CABLE