


MBT—mm



MODEL	ØD	ØP	T	L	E	A	B	H (Hex)	DRIFICE	WEIGHT (g)
MBT4M-M5	4	10.5	M5*0.8p	25.7	37.3	4.0	14.9	10	2.0	10.0
MBT4M-18R			R 1/8	29.7		8.0		10	3.0	11.0
MBT4M-14R			R 1/4	31.7		10.0		14	3.0	17.0
MBT6M-M5			M5*0.8p	28.7		4.0		12	2.0	15.0
MBT6M-18R	6	12.5	R 1/8	32.7	40.7	8.0	16.4	12	4.5	17.0
MBT6M-14R			R 1/4	35.7		10.0		14	4.5	21.0
MBT6M-38R			R 3/8	36.7		11.0		17	4.5	29.0
MBT8M-18R			R 1/8	35.4		8.0		14	6.0	21.0
MBT8M-14R	8	14.8	R 1/4	38.4	45.1	10.0	18.7	14	6.0	24.0
MBT8M-38R			R 3/8	39.4		11.0		17	6.0	31.0
MBT8M-12R			R 1/2	42.4		14.0		21	6.5	54.0
MBT10M-18R			R 1/8	37.2		8.0		17	6.0	33.0
MBT10M-14R	10	17.5	R 1/4	40.2	47.4	10.0	20.1	17	7.0	35.0
MBT10M-38R			R 3/8	41.2		11.0		17	7.0	36.0
MBT10M-12R			R 1/2	44.2		14.0		21	7.0	60.0
MBT12M-14R			R 1/4	44.6		10.0		19	7.0	47.0
MBT12M-38R	12	20.5	R 3/8	45.6	55.3	11.0	22.8	19	10.0	50.0
MBT12M-12R			R 1/2	48.6		14.0		21	10.0	60.0

MBT

Units: mm  
Scale: Full  
NITRA  
Male Branch Tee