


NEMA FRAME 284TC



DIMENSION—Inches [mm]

MOUNTING				A	B	C	D	G	J	P	L	AB	BC	AH	AA
E	2F1	2F2	H	BA											
5.5	—	9.5	0.53	4.75	14	12.5	26.64	7	0.87	2.76	13.98	16.33	12	0.25	4.38
[139.7]		[241.3]	[13.4]	[120.6]	[355.6]	[317.5]	[676.6]	[177.8]	[22]	[70.1]	[355]	[414.7]	[304.8]	[6.3]	[111.2]

KEY		KEYSET		FLANGE				SHAFT EXTENSION			TERMINAL BOX			
S	ES	R	AK	AJ	BF	BB	BD	N-W	U		XB	XC	XD	XE
0.5	3.28	1.591	10.5	9	1/2-13	0.25	11.25	4.62	1.875		3.58	7.2	6.3	8.86
[12.7]	[83.3]	[40.4]	[266.7]	[228.6]	[12.7-330.2]	[6.35]	[285.7]	[117.3]	[47.6]		[90.9]	[182.8]	[160]	[225]

MTC-025-3BD18CK

Units: inches [mm]

Scale: Full

Nema Frame
284 TC

AUTOMATIONDIRECT