


NEMA FRAME 364TC



DIMENSION-Inches [mm]


MOUNTING				A	B	C	D	G	J	P	L	AB	BC	AH	AA
E	2F1	2F2	H												
7	—	11.25	0.66	5.88	18	15.2	32.58	9	1.102	2.95	17.4	20.57	15.7	0.25	5.62
[177.8]	—	[285.7]	[16.7]	[149.3]	[457.2]	[386]	[827.5]	[228.6]	[27.9]	[74.9]	[441.9]	[522.4]	[398.7]	[6.35]	[142.7]

KEY		KEYSET		FLANGE				SHAFT EXTENSION		TERMINAL BOX				
S	ES	R	AK	AJ	BF	BB	BD	N-W	U	XB	XC	XD	XE	
0.625	4.28	2.021	12.5	11	5/8-11	0.25	14	5.88	2.375	3.74	10.55	8.98	10.83	
[15.8]	[108.7]	[51.3]	[317.5]	[279.4]	[15.8-279.4]	[6.35]	[355.6]	[149.3]	[60.3]	[94.9]	[267.9]	[228]	[275]	

MTC-0603BD18CK

Units: inches [mm]
Scale: Full

Nema Frame
364 TC

AUTOMATIONDIRECT