


NEMA FRAME 213TC



DIMENSION—Inches [mm]

MOUTING				A	B	C	D	G	J	P	L	AB	BC	AH	AA	
E	2F1	2F2	H	BA												
4.25	—	5.5	0.41	3.5	10.5	7.5	18.89	5.25	0.709	2.36	10.4	12.26	8.63	0.25	3.12	1
[107.9]	—	[139.7]	[10.4]	[88.9]	[266.7]	[190.5]	[479.8]	[133.3]	[18]	[59.9]	[264.1]	[311.4]	[219.2]	[6.3]	[79.2]	[25.4]

KEY		KEYSET	FLANGE				SHAFT EXTENSION		TERMINAL BOX				
S	ES	R	AK	AJ	BF	BB	BD	N-W	U	XB	XC	XD	XE
0.312	2.41	1.201	8.5	7.25	1/2-13	0.25	9	3.38	1.375	2.95	5	4.57	6.77
[7.9]	[61.2]	[30.4]	[215.9]	[184.1]	[12.7-330.2]	[6.3]	[228.6]	[85.8]	[34.9]	[74.9]	[127]	[116]	[171.9]

MTC-7P5-3BD18CK

Units: inches [mm]

Scale: Full

NemaFrame
213 TC

 AUTOMATIONDIRECT.com