



AC INDUCTION MOTOR, GENERAL PURPOSE AND INVERTER  
 RATED, 3HP, 3-PHASE, 208-230/460 VAC, 3600RPM, TEFC,  
 56C/HC FRAME, ROLLED STEEL, RIGID BASE/C-FACE MOUNT.

## IRONHORSE MTR PREMIUM EFFICIENCY AC MOTOR

MTRP-003-3BD36

AutomationDirect.com  
 1-800-633-0405



3rd  
ANGLE

NOT TO  
SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY  
 DUE TO MANUFACTURER'S VARIANCES

INCH UNITS USED FOR  
 PART DESIGN

UNLESS OTHERWISE  
 SPECIFIED UNITS ARE:

inch  
[mm]

LATEST VERSION  
 12/15/2022

SHEET 1 OF 1