



- 1 = TRANSMITTER DIODE
2 = RECEIVER DIODE
3 = SCREW M3 - 0.5 Nm



ISOMETRIC VIEW

NOTES:

- 1. DIMENSIONS CAN BE CHANGED BY MANUFACTURER WITHOUT NOTICE.
- 2. DIMENSIONS DO NOT IMPLY TOLERANCE.

OPT2174

Units: mm [inches]
Scale: Full
WENGLOR PHOTOELECTRIC LASER SENSOR,
DIFFUSE WITH BACKGROUND SUPPRESSION, 32 X
22 X 12MM, CLASS 1 LASER LIGHT EMISSION, 0-
1M SENSING DISTANCE, 10-30 VDC OPERATING
VOLTAGE, PNP, IO-LINK COMPATIBLE, 4-PIN M8
QUICK-DISCONNECT, 7.8IN/200MM CABLE
LENGTH

AUTOMATIONDIRECT.com