


NOTES:
1. REMOVE ALL BURRS AND SHARP EDGES

THIS DRAWING IS THE SOLE AND EXCLUSIVE PROPERTY OF ROBROY ENCLOSURES. NO PART OF THIS DRAWING MAY BE REPRODUCED, DISTRIBUTED, OR PUBLICALLY DISPLAYED IN ANY FORM OR BY ANY MEANS WITHOUT THE EXPRESS WRITTEN PERMISSION OF ROBROY ENCLOSURES. ALL RIGHTS RESERVED. UNDER THE COPYRIGHT LAWS. COPYRIGHT © 2018 ROBROY ENCLOSURES

SPECIAL REQUIREMENTS

NEMA 250: TYPE N/A IEC 60529: N/A COLOR: N/A COLOR STANDARD: N/A		STANDARD P/N: PM10-12 CUSTOMER DWG: N/A		ALL DIMENSIONS ARE IN INCHES UNLESS OTHERWISE SPECIFIED		TOLERANCES UNLESS SPECIFIED		.XX ± 0.03	.XXX ± 0.010
MATERIAL: 16 GA. CRS FINISH: POWDER COAT RAL-7541C				 A ROBROY ENCLOSURES™ BRAND		Robroy Enclosures 500 Maple Street Belding, Michigan 48809 Phone: 616-734-0700 Fax: 616-749-3378			
REVISION HISTORY									
REV	DESCRIPTION		DATE	ENG	DRAWN BY AA	DATE 5/1/18	CUSTOMER	DWG PM10-12	
A	PER ECR 6393; ADDED ADDITIONAL HOLES		1/5/18	AA					
-	-		-	-	SCALE DO NOT SCALE	DESCRIPTION POLE MOUNT BRACKET	PART NUMBER ATPM10-12		
-	-		-	-					
-	-		-	-					
-	-		-	-					



Robroy Enclosures
500 Maple Street
Belding, Michigan 48809
Phone: 616-794-0700
Fax: 616-749-3378