


THIS DRAWING IS THE SOLE AND EXCLUSIVE PROPERTY OF ROBROY ENCLOSURES. NO PART OF THIS DRAWING MAY BE REPRODUCED, DISTRIBUTED, OR PUBLICALLY DISPLAYED IN ANY FORM OR BY ANY MEANS WITHOUT THE EXPRESS WRITTEN PERMISSION OF ROBROY ENCLOSURES. ALL RIGHTS RESERVED. UNDER THE COPYRIGHT LAWS. COPYRIGHT © 2018 ROBROY ENCLOSURES

SPECIAL REQUIREMENTS

NEMA 250: TYPE N/A IEC 60529: N/A COLOR: N/A COLOR STANDARD: N/A			STANDARD P/N: PM6-8 CUSTOMER DWG: N/A			ALL DIMENSIONS ARE IN INCHES UNLESS OTHERWISE SPECIFIED			TOLERANCES UNLESS SPECIFIED			.XX ± 0.03		.XXX ± 0.010															
MATERIAL: 16 GA. CRS FINISH: POWDER COAT GRAY - 7035															 AttaBox A ROBROY ENCLOSURES™ BRAND					Robroy Enclosures 500 Maple Street Belding, Michigan 48809 Phone: 616-734-0700 Fax: 616-749-3378									
REVISION HISTORY																													
REV		DESCRIPTION				DATE		ENG		DRAWN BY AA					DATE 6/5/18					CUSTOMER					DWG PM6-8				
A		PER ECR 6393; MULTIPLE CHANGES				6/11/18		AA																					
-		-				-		-		SCALE					DESCRIPTION POLE MOUNT BRACKET					PART NUMBER ATPM6-8									
-		-				-		-																					
-		-				-		-		DO NOT SCALE					POLE MOUNT BRACKET					ATPM6-8									
-		-				-		-																					

Robroy Enclosures
500 Maple Street
Belding, Michigan 48809
Phone: 616-794-0700
Fax: 616-749-3378