




RJ45 ETHERNET



3-WIRE CONNECTOR




POWER
GREEN LED

STATUS
YELLOW LED

RESET BUTTON

22.5
[0.89]




16-WIRE CONNECTOR

49.3
[1.94]

50.7
[2.00]

120.0
[4.72]




7.2
[0.29]

100.0
[3.94]

113.9
[4.48]

6.6
[0.26]



SIO-MB04ADS

Units: mm [inches]

Scale: Full

ANALOG MODULE, 4 CHANNEL, +/-
20mA INPUT, +/-10VDC INPUT,
EXTERNAL 20-30VDC REQUIRED

AUTOMATIONDIRECT.com

NOTES:

1. DIMENSIONS CAN BE CHANGED BY MANUFACTURER WITHOUT NOTICE.
2. DIMENSIONS DO NOT IMPLY TOLERANCE.