


3X THREADED 1/4-20 X 1-3/8



BOLT CENTER

Ø2.69

[Ø68.3]

Ø3.57

[Ø90.6]

Ø3.35

[Ø85.2]

0.58  
[14.6]

0.76  
[19.2]

NOTES:

1. DIMENSIONS CAN BE CHANGED BY MANUFACTURER WITHOUT NOTICE.
2. DIMENSIONS DO NOT IMPLY TOLERANCE.

SQD28L050AF-SH

Units: inches [mm]

Scale: Full

TIMING PULLEY, L, 0.50" WIDE  
BELT, 28 TOOTH, FLANGED W/O  
HUB, DUCTILE IRON

 **AUTOMATIONDIRECT**.com