


2X THREADED 3/8-16 X 5/8




BOLT CENTER

$\phi 2.13$
[$\phi 54.1$]

$\phi 4.04$
[$\phi 102.7$]

$\phi 3.83$
[$\phi 97.3$]

$\phi 2.66$
[$\phi 67.6$]



NOTES:

1. DIMENSIONS CAN BE CHANGED BY MANUFACTURER WITHOUT NOTICE.
2. DIMENSIONS DO NOT IMPLY TOLERANCE.

STL32L100AF-1610

Units: inches [mm]

Scale: Full

TIMING PULLEY, L, 1" WIDE BELT,
32 TOOTH, FLANGED W/O HUB,
DUCTILE IRON

 **AUTOMATIONDIRECT**.com