



WIRE CONNECTION

P1		P2
2	BLUE	3
3	GREEN	5
5	ORANGE	2

TEST REQUEST:

1. OPEN SHORT 100%
2. CT ≤ 1 OHM IS ≥ 2M OHM.

NOTES: UNLESS OTHERWISE SPECIFIED

1. THIS CABLE ASSY TO BE MANUFACTURED IN COMPLIANCE WITH EU DIRECTIVE "ROHS 2002/95/EC".
2. BAG AND TAG PER MANUFACTURING REQUIREMENTS.

	ITEM LIST
①	DB 9P FEMALE CONNECTOR SHELL: FRONT NICKEL, BACK TIN INSULATOR COLOR: BLACK
②	CABLE: CAT-5 UTP 24 OR 26 AWG COLOR: BLACK
③	RJ11 6P4C PLATED GOLD 3U
④	SCREW: #4-40 UNC PD40-175TNP COLOR: BLACK
⑤	DB9 CONNECTOR OVERMOLDED WITH PVC, 65P. PE COATING.
⑥	SCREW OVERMOLDED WITH PVC, 30P, COLOR: BLACK

NOTES:

1. DIMENSIONS CAN BE CHANGED BY MANUFACTURER WITHOUT NOTICE.
2. DIMENSIONS DO NOT IMPLY TOLERANCE.

STP-232RJ11-CBL

Units: mm [inches]

Scale: Full

SURESTEP 10 FOOT LENGTH
PROGRAMMING/COM CABLE, 9-PIN D-SUB
FEMALE TO 6P4C RJ11 FOR USE WITH
STP-DRV-80100 and STP-DRV-4850 DRIVES

AUTOMATIONDIRECT.com