


| CABLE LENGTH TABLE |         |     |        |        |
|--------------------|---------|-----|--------|--------|
| MARK               | PART NO | REV | 'L' FT | 'L' MM |
| STP-CBL-CA6        |         |     | 6      | 1829   |
| STP-CBL-CA10       |         |     | 10     | 3048   |
| STP-CBL-CA20       |         |     | 20     | 6096   |

| C 1     |        |            |
|---------|--------|------------|
| PIN NO: | SIGNAL | WIRE COLOR |
| 1       | STEP+  | GRAY/PINK  |
| 2       | STEP-  | BROWN      |
| 3       | DIR+   | YELLOW     |
| 4       | DIR-   | GREEN      |
| 5       | EN+    | BLUE       |
| 6       | EN-    | RED/BLUE   |
| 7       | OUT+   | GRAY       |
| 8       | OUT-   | WHITE      |
| 9       | N.C.   | PINK       |
| 10      | V-     | BLACK      |
| 11      | V+     | RED        |



#### NOTES:

1. DIMENSIONS CAN BE CHANGED BY MANUFACTURER WITHOUT NOTICE.
2. DIMENSIONS DO NOT IMPLY TOLERANCE.

| STP-CBL-CA10   |
|--|
| Units: mm [inches]   |
| Scale: Full  |
| CABLE FOR SURESTEP<br>STP-MTRD-17038 AND<br>STP-MTRD-17038E INTEGRATED<br>STEPPER MOTOR/DRIVES, 10FT |
| <b>AUTOMATIONDIRECT</b> .com   |