



VIEW FROM WIRE ENTRANCE

| PIN # | COLOR | PHASE |
|-------|-------|-----------|
| 1 | RED | A |
| 2 | WHITE | \bar{A} |
| 3 | GREEN | B |
| 4 | BLACK | \bar{B} |

STP-MTR-23055D Rev B

Units: inches [mm]

Scale: Full

SureStep STEPPER MOTOR, NEMA 23
166 OZ-IN, 2.8 AMP/PHASE, IP40,
DUAL SHAFT, BIPOLAR

AUTOMATIONDIRECT.com