



## STP-MTRAC-42151

Units: inches [mm]

Scale: Full

SureStep STEPPER MOTOR, NEMA 42  
FRAME, IP40, SINGLE SHAFT, 6A, 3116  
OZ-IN HOLDING TORQUE, 1.8-DEGREE  
STEP ANGLE, 200 STEPS PER REV,  
BIPOLAR

**AUTOMATIONDIRECT** INC.

### NOTES:

1. DIMENSIONS CAN BE CHANGED BY MANUFACTURER WITHOUT NOTICE.
2. DIMENSIONS DO NOT IMPLY TOLERANCE.