



STP-MTRAC-42202

Units: inches [mm]

Scale: Full

SureStep STEPPER MOTOR, NEMA 42
FRAME, IP40, SINGLE SHAFT, 6A, 4390
OZ-IN HOLDING TORQUE, 1.8-DEGREE
STEP ANGLE, 200 STEPS PER REV,
BIPOLAR

AUTOMATIONDIRECT COM

NOTES:

1. DIMENSIONS CAN BE CHANGED BY MANUFACTURER WITHOUT NOTICE.
2. DIMENSIONS DO NOT IMPLY TOLERANCE.