



VIEW FROM WIRE ENTRANCE

PIN #	COLOR	PHASE
1	RED	A
2	WHITE	\bar{A}
3	GREEN	B
4	BLACK	\bar{B}

STP-MTRH-23079D RevB

Units: inches [mm]

Scale: Full

SureStep STEPPER MOTOR, NEMA 23
286 OZ-IN, 5.6 AMP/PHASE, IP40,
DUAL SHAFT, BIPOLAR

AUTOMATIONDIRECT.com