

SECTION A-A

SECTION B-B


THIS DRAWING IS THE SOLE AND EXCLUSIVE PROPERTY OF ROBROY ENCLOSURES. NO PART OF THIS DRAWING MAY BE REPRODUCED, DISTRIBUTED, OR PUBLICALLY DISPLAYED IN ANY FORM OR BY ANY MEANS WITHOUT THE EXPRESS WRITTEN PERMISSION OF ROBROY ENCLOSURES. ALL RIGHTS RESERVED. UNDER THE COPYRIGHT LAWS. COPYRIGHT © 2020 ROBROY ENCLOSURES.

SPECIAL REQUIREMENTS

CNC:
1. CONTACT ENGINEERING FOR FIRST RUN INSPECTION

ASSEMBLY:

1. INSTALL (1) QT-LATCH (RMEMKSE) AS SHOWN PER STANDARD PROCESS
2. INSTALL (2) (RMLATNLL150) & (2) (RMLATNLL150WT) LATCHES ON BOX & (4) KEEPERS (RMKEEPLL150WT) ON COVER USING (16) RIVET (RMRIV46) PER STANDARD PROCESS

NEMA 250: TYPE 1, 3, 3R, 4X, 12 IEC 60529: IP66		STANDARD P/N: T363012HWTSL		ALL DIMENSIONS ARE IN INCHES UNLESS OTHERWISE SPECIFIED		TOLERANCES UNLESS SPECIFIED		.XX ± 0.03	XXX ± 0.010
COLOR: GLACIER GRAY (WPR3X13) COLOR STANDARD: PANTONE 428 C		CUSTOMER DWG:		<div> AttoBox A ROBROY ENCLOSURES™ BRAND</div> <div><div>DRAWN BY AA</div><div>DATE 8/17/20</div><div>CUSTOMER</div></div> <div><div>SCALE DO NOT SCALE</div><div>DESCRIPTION STANDARD ENCLOSURE</div><div>PART NUMBER ATT363012HWTSL</div></div>					
MATERIAL: FIBERGLASS REINFORCED POLYESTER (FRP)									
REVISION HISTORY									
REV	DESCRIPTION	DATE	ENG						
-	-	-	-						
-	-	-	-						
-	-	-	-						
-	-	-	-						
-	-	-	-						
-	-	-	-						
-	-	-	-						
DRAWN BY AA		DATE 8/17/20		CUSTOMER		DWG T363012HWTSL			
SCALE DO NOT SCALE		DESCRIPTION STANDARD ENCLOSURE		PART NUMBER ATT363012HWTSL		Robroy Enclosures 500 Maple Street Belding, Michigan 48809 Phone: 616-734-0700 Fax: 616-749-3378			

