



CUTOUT TEMPLATE VIEWED FROM INSIDE ENCLOSURE. FLIP IF APPLIED TO OUTSIDE OF ENCLOSURE.

TE20-015-24D-04

Units: inches [mm]

Scale: Full

ENCLOSURE HEAT EXCHANGER,
1446 BTU/H, 24VDC, SIDE MOUNT,
ANSI 61 FOR UL TYPE 4 ENCLOSURE

AUTOMATIONDIRECT.com