


1.75 in
[44 mm]


Ø .27 in
[7 mm]

TOP VIEW




Ø.28 in x .78 in
SLOT, TYP

ISOMETRIC




FRONT VIEW

Ø .18 in
[4 mm]
#10-32 TAPPED, TYP



R.S. VIEW

.25 in [6 mm] .62 in [16 mm] .62 in [16 mm] .50 in [13 mm]



10:1

1.75 in
[44 mm]
TYP EIA SPACING

RACK UNIT INDICATOR

PART NUMBERS	
URR27U	PAINTED BLACK THIN FILM
NOTES	
SOLD AS PAIR	
MOUNTING HARDWARE NOT INCLUDED	
RACK UNITS MARKED	
SEE HAMMOND WEBSITE FOR MORE INFORMATION	
Français	
Pour tous les détails sur nos produits, svp veuillez consulter notre site www.hammondmfg.com	
Data subject to change without notice. Isometric drawing not to scale. Les données sont sujettes à changement sans préavis.	
<div> HAMMOND MANUFACTURING®</div> <div> www.hammondmfg.com</div>	
PART NO.	URR27U

