


TABLE A	
PART NUMBER	L
USB-CBL-AMICB6	6FT
USB-CBL-AMICB15	15FT



Notes:

1. (USB2.0) UL2725 28AWG*1 Pair+28AWG*2C+AEB. OD: 3.8MM, Jacket Black

2. USB Type A Male Soldering Type.

Insulation: PBT, White Color

Contact: Brass Gold-Plated (30u")

Shell Nickel Plated

3. USB Micro Type B Male Soldering Type.

Insulation: PBT, White Color

Contact: Brass Gold-Plated (30u")

Shell Nickel Plated

4: Minimum Bend Radius - 26.6 mm [1.04 in]

USB-CBL-AMICB6	
Rev: B	Date: 1/2/2014
Units: mm [inches]	
Scale: 1:1	
P2000 USB PROGRAMMING CABLE	