







Automation Direct Part #	Max Voltage	Amps	Phase	Weight (LBS)
VTF-46-DE	600	2	3	8
VTF-246-CFG	600	3	3	8
VTF-246-DGH	600	4	3	8
VTF-24-FH1	600	6	3	8
VTF-246-GJJ	600	8	3	8
VTF-246-HKL	600	12	3	8



(Customer Connections)
Markings On Terminal Block
For Reference Only.



Note: Maintain Clearance of 3 Inches On All Sides To Other Equipment.

See VTF Installation Guide For
Terminal Wire Size And Torque Information.

Customer Is Responsible For Installation to
Meet All National And Local Electrical Codes.

Material(s) Shall be RoHS Compliant

NOTES:

1. DIMENSIONS CAN BE CHANGED BY MANUFACTURER WITHOUT NOTICE.
2. DIMENSIONS DO NOT IMPLY TOLERANCE.

VTF-246-GJJ

Units: inches [mm]

Scale: Full

VTF SERIES OUTPUT FILTER
230/460/575 VAC 2HP, 5HP, 3-PHASE,
8A, OUTPUT SIDE ONLY, REV B

AUTOMATIONDIRECT.com