







Automation Direct Part #	Max Voltage	Amps	Phase	Weight (LBS)
VTF-46-DE	600	2	3	8
VTF-246-CFG	600	3	3	8
VTF-246-DGH	600	4	3	8
VTF-24-FH	600	6	3	8
VTF-246-GJJ	600	8	3	8
VTF-246-HKL	600	12	3	8



(Customer Connections)  
Markings On Terminal Block  
For Reference Only.



Note: Maintain Clearance of 3 Inches On All Sides To Other Equipment.

See VTF Installation Guide For  
Terminal Wire Size And Torque Information.

Customer Is Responsible For Installation to  
Meet All National And Local Electrical Codes.

Material(s) Shall be RoHS Compliant

#### NOTES:

1. DIMENSIONS CAN BE CHANGED BY MANUFACTURER WITHOUT NOTICE.
2. DIMENSIONS DO NOT IMPLY TOLERANCE.

VTF-46-DE

Units: inches [mm]

Scale: Full

VTF SERIES OUTPUT FILTER  
460/575 VAC 3/4HP, 1HP, 3-PHASE,  
2A, OUTPUT SIDE ONLY, REV B

