


TABLE A

PART NO.	LENGTH
ZL-BXEM-CBL20	0.5m (1.7ft)
ZL-BXEM-CBL20-1	1.0m (3.3ft)
ZL-BXEM-CBL20-2	2.0m (6.6ft)



NOTES:

1. CABLE: 24 CONDUCTOR, 24 AWG, PVC JACKET INSULATION RATING 80°C (176°F), 300V
2. CURRENT: 2A PER CONDUCTOR, 40A MAXIMUM CABLE CURRENT
3. VOLTAGE
 - 240V AC/DC RATED OPERATING VOLTAGE
 - 265V AC/DC MAXIMUM VOLTAGE
4. OPERATING TEMPERATURE: 0-60°C (32-140°F)
5. P1 CONNECTOR: 20 POSITION OVERMOLDED TERMINAL BLOCK FOR BRX PLC
6. P2 CONNECTOR: 24-PIN RECEPTACLE EQUIVALENT TO MOLEX MICRO-FIT3.0 (PART # 43025-2400)
7. MINIMUM BEND RADIUS: 65.6MM [2.58IN]

ZL-BXEM-CBL20-n

Rev: A Date: 4/5/2016

Units: mm [inches]

Scale: 1:1

ZIPLink
Connector Module Cable

AUTOMATION DIRECT