


TABLE A

PART NO.	LENGTH
ZL-CBL50-1P	1.0m (3.3ft)
ZL-CBL50-2P	2.0m (6.6ft)



PIN-OUT DIAGRAM

P1		P1	
1	Black	14	Pink/Blue
26	Black/White	39	Pink/Green
2	Brown	15	Light Blue
27	Brown/White	40	Light Yellow
3	Red	16	Light Blue/Black
28	Red/White	41	Light Blue/Red
4	Orange	17	Light Blue/Blue
29	Orange/White	42	Light Blue/Green
5	Yellow	18	Grey/Red
30	Yellow/Black	43	Grey/Green
6	Green	19	Blue/Black
31	Green/White	44	Purple/Black
7	Blue	20	Light Green/Black
32	Blue/White	45	Light green/Red
8	Purple	21	Light Green/Blue
33	Purple/White	46	Light Green/Green
9	Grey	22	Light Yellow/Black
34	Grey/Black	47	Light Yellow/Red
10	White	23	Light Yellow/Blue
35	Orange/Black	48	Light Yellow/Green
11	Pink	24	White/Black
36	Red/Black	49	White/Red
12	Light Green	25	White/Blue
37	Green/Black	50	White/green
13	Pink/Black		
38	Pink/Red		

NOTES:

- CABLE: 50 CONDUCTOR, 28 AWG, BLACK PVC JACKET INSULATION RATING 80°C (176°F), 30V
- VOLTAGE
  - AC/DC RATED OPERATING VOLTAGE 24V
  - AC/DC MAXIMUM VOLTAGE 30V
- OPERATING TEMPERATURE: 0-60°C (32-140°F)
- P1 CONNECTOR:
  - HPCN-50M MALE PIN/5U" BLACK
  - NICKEL-SHELL PH:1.27MM
  - IDC-ASSEMBLY TYPE OD: 9.0MM (MMS50113)
- MINIMUM BEND RADIUS: 64MM [2.52IN]

ZL-CBL50-nP	
Rev: D	Date: 11/9/2016
Units: mm [inches]	
Scale: 1:1	
ZIPLink High Density Cable	