


TABLE A

PART NO	LENGTH
ZL-D0-CBL24-P	0.5m [1.6 ft]
ZL-D0-CBL24-1P	1.0m [3.3 ft]
ZL-D0-CBL24-2P	2.0m [6.6 ft]



NOTES:

1. CABLE – 24 conductor, 24 AWG, PVC jacket insulation rating 80°C (176°F), 300V
2. CURRENT – 2A per conductor, 40A maximum cable current
3. VOLTAGE –
240V AC/DC rated operating voltage
265V AC/DC maximum voltage
4. OPERATING TEMPERATURE – 0–60°C (32–140°F)
5. P1 CONNECTOR – 24-pin receptacle equivalent to Molex Micro-Fit3.0 part # 43025–2400
6. P2 CONNECTOR– PIG TAIL
7. MINIMUM BEND RADIUS – 65.6mm [2.58"]

PIN-OUT DIAGRAM

P1	P2	P1	P2
1 ——— BLUE		13 ——— ORANGE/BLACK	
2 ——— PINK		14 ——— RED/BLACK	
3 ——— LIGHT BLUE		15 ——— WHITE	
4 ——— LIGHT GREEN		16 ——— GREEN/BLACK	
5 ——— GRAY		17 ——— GRAY/BLACK	
6 ——— YELLOW		18 ——— YELLOW/BLACK	
7 ——— PURPLE		19 ——— PURPLE/WHITE	
8 ——— GREEN		20 ——— GREEN/WHITE	
9 ——— ORANGE		21 ——— ORANGE/WHITE	
10 ——— RED		22 ——— RED/WHITE	
11 ——— BROWN		23 ——— BROWN/WHITE	
12 ——— BLACK		24 ——— BLACK/WHITE	

ZL-D0-CBL24-nP

Rev: original Date: 07/2009

Units: mm [inches]

Scale: .03940

ZIPLINK DL05/DL06 Cable

