


TABLE A

PART NO	LENGTH
ZL-D24-CBL40	0.5m [1.6 ft]
ZL-D24-CBL40-1	1.0m [3.3 ft]
ZL-D24-CBL40-2	2.0m [6.6 ft]



PIN-OUT DIAGRAM

P1		P2		P1		P2	
1	BLACK	1		21	BLACK/WHITE	21	
2	BROWN	2		22	BROWN/WHITE	22	
3	RED	3		23	RED/WHITE	23	
4	ORANGE	4		24	ORANGE/WHITE	24	
5	GREEN	5		25	GREEN/WHITE	25	
6	PURPLE	6		26	PURPLE/WHITE	26	
7	BLUE	7		27	BLUE/WHITE	27	
8	GRAY	8		28	GRAY/BLACK	28	
9	LIGHT GREEN	9		29	LIGHT GREEN /BLACK	29	
10	YELLOW	10		30	YELLOW/BLACK	30	
11	PINK	11		31	PINK/BLACK	31	
12	LIGHT BLUE	12		32	LIGHT BLUE /BLACK	32	
13	PINK/RED	13		33	PINK/GREEN	33	
14	LIGHT BLUE /RED	14		34	LIGHT BLUE /GREEN	34	
15	GRAY/RED	15		35	GRAY/GREEN	35	
16	LIGHT GREEN /RED	16		36	LIGHT GREEN /GREEN	36	
17	PINK/BLUE	17		37	LIGHT BLUE /BLUE	37	
18	PURPLE/BLACK	18		38	BLUE/BLACK	38	
19	RED/BLACK	19		39	ORANGE/BLACK	39	
20	WHITE	20		40	GREEN/BLACK	40	

NOTES:

1. CABLE – 40 conductor, 26 AWG, PVC jacket insulation rating 80°C (176°F), 300V
2. CURRENT – 0.5A per conductor, 32A maximum cable current
3. VOLTAGE –
24V AC/DC rated operating voltage
30V AC/DC maximum voltage
4. OPERATING TEMPERATURE – 0–60°C (32–140°F)
7. P1 CONNECTOR – Fujitsu soldering type jack for FCN-360 series, AutomationDirect Order # ZL-D24-CON
8. P2 CONNECTOR – Equivalent to 3M 34000 Series IDC Connector, Strain relief is required to latch to header.
Example: Socket 3417-7640, Strain relief 3448-3040
9. MINIMUM BEND RADIUS – 80 mm [3.15 in]

ZL-D24-CBL40-x

Rev: E4

Date: 06/2009

Units: mm [inches]

Scale: .03940

ZIPLINK D2 & D4 PLC CABLE

