



PIN OUT

P1	P2
1	BLACK
2	BROWN
3	RED
4	ORANGE
5	YELLOW
6	GREEN
7	BLUE
8	VIOLET
9	GREY

NOTES:

1. CABLE – 9 conductor, 28 AWG, UL2464, OD:5.0MM, PVC black jacket
2. VOLTAGE –
DC rated operating voltage 24VDC
DC maximum voltage 30VDC
AC rated operating voltage 120VAC
AC maximum voltage 150VAC
3. OPERATING TEMPERATURE – 0–60°C (32–140°F)
4. P2 CONNECTOR – DB–9F FEMALE BLACK PIN/GF SHELL–NICKEL PLATING
5. MINIMUM BEND RADIUS – 40mm [1.57in]

ZL-DB9F-CBL-2P

Units: mm [in]

Scale: none

ZIPLINK DB9F
to Pigtail Cable

 **AUTOMATIONDIRECT**.com