




WIRING	
COLOR	FUNCTION
J1 - +	V+ (ALL PORTS PIN 1)
J1 - -	V- (ALL PORTS PIN 3)
J1-GND	GND (ALL PORTS PIN 5)
J2 - 1	PORT 1 PIN 4
J2 - 2	PORT 2 PIN 4
J2 - 3	PORT 3 PIN 4
J2 - 4	PORT 4 PIN 4
J3 - 1	PORT 1 PIN 2
J3 - 2	PORT 2 PIN 2
J3 - 3	PORT 3 PIN 2
J3 - 4	PORT 4 PIN 2
VOLTS AMPS	48 VDC MAX 3A PER PORT, 8A PER BLOCK



CONNECTIONS MADE  
VIA SPRING CLAMP  
TERMINAL BLOCKS

MATERIALS	
BODY	PBT
MARKERS	POLYAMIDE
INSERTS	POLYAMIDE
GLAND	POLYAMIDE
CONTACTS	GOLD PLATED COPPER ALLOY
O-RINGS	NBR



THIS IS A LIGHTED PNP BLOCK

ZP-JBH45-2P-FW

Units: inches [mm]

Scale: 1:1

ZIP-Port Junction Block