



WIRING	
COLOR	FUNCTION
BROWN	V+ (ALL PORTS PIN 1)
BLUE	V- (ALL PORTS PIN 3)
GREEN/YELLOW	GND (ALL PORTS PIN 5)
WHITE	PORT 1 PIN 4
GREEN	PORT 2 PIN 4
YELLOW	PORT 3 PIN 4
GRAY	PORT 4 PIN 4
PINK	PORT 5 PIN 4
RED	PORT 6 PIN 4
GRAY / PINK	PORT 1 PIN 2
RED / BLUE	PORT 2 PIN 2
WHITE / GRN	PORT 3 PIN 2
BROWN / GRN	PORT 4 PIN 2
WHITE / YEL	PORT 5 PIN 2
YEL / BROWN	PORT 6 PIN 2
VOLTS	48 VDC MAX
AMPS	3A PER PORT, 8A PER BLOCK



MATERIALS	
BODY	PBT
MARKERS	POLYAMIDE
INSERTS	POLYAMIDE
GLAND	POLYAMIDE
CONTACTS	GOLD PLATED COPPER ALLOY
O-RINGS	NBR

ZIP-JBH65-2P-5
Units: inches [mm]
Scale: 1:1
ZIP-Port Junction Block

AUTOMATIONDIRECT
.com

THIS IS A LIGHTED PNP BLOCK