




PANEL CUTOOUT



USB TYPE B FEMALE
TD TYPE A FEMALE



STANDARD CONFIGURATIONS UNLESS OTHERWISE NOTED
 CONNECTION TYPE EXTERIOR INTERIOR
 ALL D-SUBS FEMALE MALE

PICK RATINGS
 VOLTS 115V
 AMPS 3A
 SCCR 10KA
 NEMA VUL 4,4X,12

BODY EPDXY COATED DIE CAST ALUMINUM
 GASKET THERMOPLASTIC ELASTOMER
 HANDLE POLYAMIDE
 LEVERS STAINLESS STEEL

ZP-PDA-32-400

Units: inches [mm]

Scale: Full

ZP-PDA-32-400

