




PANEL CUTOUT



STANDARD CONFIGURATIONS UNLESS OTHERWISE NOTED

CONNECTION TYPE	EXTERIOR	INTERIOR
RJ 45	CAT 5 JACK	CAT 5 JACK

PICK RATINGS	
VOLTS	115V
AMPS	3A
SCCR	10KA
NEMA VUL	4, 4X, 12

BODY	EPDOY COATED DIE CAST ALUMINUM
GASKET	THERMOPLASTIC ELASTOMER
HANDLE	POLYAMIDE
LEVERS	STAINLESS STEEL

ZP-PDA-32-402

Units: inches [mm]

Scale: Full

ZP-PDA-32-402

