




PANEL CUTOOUT



For power connector, crimp terminals are supplied for hot and neutral connection. Ground wire supplied with an M3 ring terminal applied to end of 6" ground lead.



STANDARD CONFIGURATIONS UNLESS OTHERWISE NOTED  
 CONNECTION TYPE EXTERIOR INTERIOR  
 RJ 45 CAT 5 JACK CAT 5 JACK

PICK RATINGS  
 VOLTS 115V  
 AMPS 15A  
 SCRR 10KA  
 NEMA/VUL 4,4X,12

BODY EPDXY COATED DIE CAST ALUMINUM  
 GASKET THERMOPLASTIC ELASTOMER  
 HANDLE POLYAMIDE  
 LEVERS STAINLESS STEEL

ZP-PSA-16-101

Units: inches [mm]  
 Scale: Full

ZP-PSA-16-101