




PANEL CUTOUT



Note: RJ 11 JACK IS TECHNICALLY AN RJ 12 JACK IN THAT IT HAS ALL 6 CONTACTS. IT IS SUITABLE FOR USE WITH ALL RJ 11 AND RJ 12 APPLICATIONS.

For power connector, crimp terminals are supplied for hot and neutral connection. Ground wire supplied with an M3 ring terminal applied to end of 6' ground lead.

STANDARD CONFIGURATIONS UNLESS OTHERWISE NOTED

CONNECTION TYPE	EXTERIOR JACK	INTERIOR JACK
RJ 11		

PICK RATINGS	BODY
VOLTS 115V	EPDXY COATED DIE CAST ALUMINUM
AMPS 15A	GASKET THERMOPLASTIC ELASTOMER
SCCR 10KA	HANDLE POLYAMIDE
NEMA/VOL 4,4X,12	LEVERS STAINLESS STEEL

ZP-PSA-16-102

Units: inches [mm]
Scale: Full

ZP-PSA-16-102