




PANEL CUTOUT



For power connector, crimp terminals are supplied for hot and neutral connection. Ground wire supplied with an M3 ring terminal applied to end of 6" ground lead.

STANDARD CONFIGURATIONS UNLESS OTHERWISE NOTED

CONNECTION TYPE	EXTERIOR	INTERIOR
ALL D-SUBS	FEMALE	MALE

PICK RATINGS	BODY
VOLTS 115V	EPDXY COATED DIE CAST ALUMINUM
AMPS 15A	GASKET THERMOPLASTIC ELASTOMER
SCCR 10KA	HANDLE POLYAMIDE
NEMA/VOL 4, 4X, 12	LEVERS STAINLESS STEEL

ZP-PSA-16-103

Units: inches [mm]
Scale: Full

ZP-PSA-16-103