




PANEL CUTOUT



For power connection, crimp terminals are supplied for hot and neutral connection. Ground wire supplied with an M3 ring terminal applied to end of 6' ground lead.



STANDARD CONFIGURATIONS UNLESS OTHERWISE NOTED

CONNECTION TYPE EXTERIOR INTERIOR
ALL D-SUBS FEMALE MALE

PICK RATINGS
VOLTS 115V
AMPS 15A
SCCR 10KA
NEMA/VOL 4,4X,12

BODY EPDXY COATED DIE CAST ALUMINUM
GASKET THERMOPLASTIC ELASTOMER
HANDLE POLYAMIDE
LEVERS STAINLESS STEEL

ZP-PSA-16-104

Units: inches [mm]
Scale: Full

ZP-PSA-16-104