


PANEL CUTOUT



For power connector, crimp terminals are supplied for hot and neutral connection. Ground wire supplied with an M3 ring terminal applied to end of 6' ground lead.

PICK RATINGS	BODY	EPDXY COATED DIE CAST ALUMINUM
VOLTS 115V	GASKET	THERMOPLASTIC ELASTOMER
AMPS 3A	HANDLE	POLYAMIDE
SCCR 10KA	LEVERS	STAINLESS STEEL
NEMA IUL 4, 4X, 12		

STANDARD CONFIGURATIONS UNLESS OTHERWISE NOTED		
CONNECTION TYPE	EXTERIOR	INTERIOR
ALL D-SUBS	FEMALE	MALE

ZP-PSA-16-200

Units: inches [mm]

Scale: Full

ZP-PSA-16-200