



NOTES:

1. DIMENSIONS CAN BE CHANGED BY MANUFACTURER WITHOUT NOTICE.
2. DIMENSIONS DO NOT IMPLY TOLERANCE.

S8-MR-5-W13-PP

Units: mm [inch]

Full Scale

DATALOGIC CONTRAST SENSOR, PRINT MARK, RGB LIGHT EMISSION, 7-11MM SENSING DISTANCE, PNP, 25 KHZ SWITCHING FREQUENCY, 316L STAINLESS STEEL HOUSING, 4-PIN M8 QUICK-DISCONNECT.

AUTOMATIONDIRECT.com