



NOTES:

1. DIMENSIONS CAN BE CHANGED BY MANUFACTURER WITHOUT NOTICE.
2. DIMENSIONS DO NOT IMPLY TOLERANCE.

TL46-WL-815
Units: mm [inch]
Full Scale
DATALOGIC CONTRAST SENSOR, PRINT MARK, RGB LIGHT EMISSION, VERTICAL SPOT ORIENTATION, 6-12MM SENSING DISTANCE, NPN / PNP, 20 KHZ SWITCHING FREQUENCY, ALUMINUM HOUSING, 5-PIN M12 QUICK-DISCONNECT.
<b>AUTOMATIONDIRECT</b> .com