



LINE SIDE



LOAD SIDE

Metric +/- 0.13mm
Inches +/- 0.005"
Angular +/- 2°

| HPB104-1 |
|--|
| Units: mm [inch] Full Scale |
| DISTRIBUTION BLOCK OPEN STYLE, UL LISTED 175A, 1 POLE, 1-IN, 4-OUT |
| AUTOMATIONDIRECT .com |