




PANEL CUTOUT



STANDARD CONFIGURATIONS UNLESS OTHERWISE NOTED

CONNECTION TYPE	EXTERIOR	INTERIOR
ALL D-SUBS	FEMALE	MALE

PICK RATINGS

VOLTS	115V
AMPS	3A
SCCR	10KA
NEMA VUL	4, 4X, 12

BODY

EPDXY COATED DIE CAST ALUMINUM

GASKET

THERMOPLASTIC ELASTOMER

HANDLE

POLYAMIDE

LEVERS

STAINLESS STEEL

ZP-PDA-32-401

Units: inches [mm]
Scale: Full

ZP-PDA-32-401

