




PANEL CUTOUT



USB TYPE A FEMALE
TD TYPE A FEMALE



STANDARD CONFIGURATIONS UNLESS OTHERWISE NOTED

CONNECTION TYPE	EXTERIOR	INTERIOR
ALL D-SUBS	FEMALE	MALE

PICK RATINGS

VOLTS	115V
AMPS	3A
SCCR	10KA
NEMA VUL	4, 4X, 12

BODY

GASKET	EPDXY COATED DIE CAST ALUMINUM
HANDLE	THERMOPLASTIC ELASTOMER
LEVERS	POLYAMIDE
	STAINLESS STEEL

ZP-PDA-32-305

Units: inches [mm]
Scale: Full

ZP-PDA-32-305