




PANEL CUTOUT



9 PIN D-SUB IS CONNECTED TO A 3 PIN PLUGGABLE
TERMINAL BLOCK FOR BLUE HOSE APPLICATION



STANDARD CONFIGURATIONS UNLESS OTHERWISE NOTED

CONNECTION TYPE	EXTERIOR	INTERIOR
RJ 45	CAT 5 JACK	CAT 5 JACK

PICK RATINGS

VOLTS	115V
AMPS	3A
SCCR	10KA
NEMA VUL	4, 4X, 12

BODY

GASKET	EPDXY COATED DIE CAST ALUMINUM
HANDLE	THERMOPLASTIC ELASTOMER
LEVERS	POLYAMIDE
	STAINLESS STEEL

ZP-PDA-32-304

Units: inches [mm]
Scale: Full

ZP-PDA-32-304