




PANEL CUTOUT



STANDARD CONFIGURATIONS UNLESS OTHERWISE NOTED

CONNECTION TYPE	EXTERIOR	INTERIOR
ALL D-SUBS	FEMALE	MALE

PICK RATINGS

VOLTS	115V
AMPS	3A
SCRR	10KA
NEMA VUL	4, 4X, 12

BODY

GASKET	EPOXY COATED DIE CAST ALUMINUM
HANDLE	THERMOPLASTIC ELASTOMER
LEVERS	POLYAMIDE
	STAINLESS STEEL

ZP-PSA-32-200

Units: inches [mm]

Scale: Full

ZP-PSA-32-200