




PANEL CUTOUT



NOTE: RJ 11 JACK IS TECHNICALLY AN RJ 12 JACK
IN THAT IT HAS ALL 6 CONTACTS.
IT IS SUITABLE FOR USE WITH ALL RJ 11
AND RJ 12 APPLICATIONS



STANDARD CONFIGURATIONS UNLESS OTHERWISE NOTED

CONNECTION TYPE	EXTERIOR JACK	INTERIOR JACK
ALL D-SUBS		
RJ 11		

PICK RATINGS
VOLTS 115V
AMPS 3A
SCCR 10KA
NEMA VUL 4, 4X, 12

BODY	EPDXY COATED DIE CAST ALUMINUM
GASKET	THERMOPLASTIC ELASTOMER
HANDLE	POLYAMIDE
LEVERS	STAINLESS STEEL

ZP-PDA-32-403

Units: inches [mm]

Scale: Full

ZP-PDA-32-403